



SURFACE VEHICLE RECOMMENDED PRACTICE

J968™-1

SEP2015

Issued 1966-08
Revised 1991-05
Reaffirmed 2015-09

Superseding J968-1 DEC2002

Diesel Injection Pump Testing - Part 1: Calibrating Nozzle and Holder Assemblies

RATIONALE

J968-1 has been reaffirmed to comply with the SAE five-year review policy.

Foreword—This SAE Recommended Practice is similar to ISO 7440/1.

The calibrating nozzle and holder assemblies are intended to simulate closely the function of the nozzle and holder assemblies in the fuel injection system of a diesel engine. They are flow gauges and require careful handling and maintenance.

The manufacturer of the injection equipment and/or the manufacturer of the engine shall specify the type of calibrating nozzle and holder assembly, the appropriate single hole orifice plate size or pintle nozzle (as applicable), high pressure pipes, exact limits, etc., to be used.

1. **Scope**—This part of SAE J968 specifies two types of calibrating nozzle and holder assemblies intended for the testing and setting of diesel injection pumps on test benches.

It applies to:

- a. A calibrating nozzle and holder assembly with a single hole orifice plate;
- b. A calibrating nozzle and holder assembly with a delay pintle type nozzle.

The approximate range of the calibrating nozzle and holder assembly is up to:

- a. 300 mm³/stroke with the single hole orifice plate;
- b. 150 mm³/stroke with the delay pintle type nozzle.

Setting and maintenance requirements are specified in ISO 4008/3.

2. References

- 2.1 **Applicable Publications**—The following publications form a part of this specification to the extent specified herein. The latest issue of SAE publications shall apply.

- 2.1.1 SAE PUBLICATIONS—Available from SAE, 400 Commonwealth Drive, Warrendale, PA 15096-0001.

SAE J967—Calibration Fluid for Diesel Injection Equipment

SAE J968-2—Diesel Injection Pump Testing—Part 2: Orifice Plate Flow Measurement

SAE Technical Standards Board Rules provide that: "This report is published by SAE to advance the state of technical and engineering sciences. The use of this report is entirely voluntary, and its applicability and suitability for any particular use, including any patent infringement arising therefrom, is the sole responsibility of the user."

SAE reviews each technical report at least every five years at which time it may be revised, reaffirmed, stabilized, or cancelled. SAE invites your written comments and suggestions.

Copyright © 2015 SAE International

All rights reserved. No part of this publication may be reproduced, stored in a retrieval system or transmitted, in any form or by any means, electronic, mechanical, photocopying, recording, or otherwise, without the prior written permission of SAE.

TO PLACE A DOCUMENT ORDER: Tel: 877-606-7323 (inside USA and Canada)
Tel: +1 724-776-4970 (outside USA)
Fax: 724-776-0790
Email: CustomerService@sae.org
http://www.sae.org

SAE WEB ADDRESS:

SAE values your input. To provide feedback
on this Technical Report, please visit
http://www.sae.org/technical/standards/J968/1_201509

2.1.2 ISO PUBLICATIONS—Available from ANSI, 25 West 43nd Street, New York, NY 10036-8002.

ISO 2697—Road vehicles—Fuel injection nozzles—Size “S”

ISO 2699—Road vehicles—Flange-mounted injection nozzle holders size “S”—Types 2, 3, 4, 5, and 6

ISO 4008/3—Road vehicles—Fuel injection pump testing—Part 3: Application and test procedures

ISO 4010—Road vehicles—Calibrating nozzle, delay pintle type

ISO 4093—Road vehicles—Fuel injection pumps—High pressure pipes for testing

ISO 4113—Road vehicles—Calibration fluid for diesel injection equipment

ISO 7440/1—Road vehicles—Fuel injection equipment testing—Part 1: Calibrating nozzle and holder assemblies

ISO 7440/2—Road vehicles—Fuel injection equipment testing—Part 2: Orifice plate flow-measurement

3. **Required Characteristics**—The functionally critical dimensions are shown in the following diagrams:

3.1 **Calibrating Nozzle and Holder Assemblies**

With single hole orifice plate, Figure 1.

With delay pintle type nozzle, Figure 2.

3.2 **Components**

Holder body with and without vent, Figure 3.

Spring, standard, and low rate, Figure 4.

Inlet stud with edge filter, Figure 5.

Suggested edge filter flow measuring system, Figure 6.

NOTE—The outlet of the fixture (within the dotted lines) shall be at ambient pressure.

Needle valve assembly, Figure 7.

Single hole orifice plate and flow ranges, Figure 8.

Delay pintle type nozzle is specified in ISO 4010.

Distance sleeve, Figure 9.

Retaining nuts, Figures 10 and 11.

4. **Designation**

4.1 **General Example**—There are many possible combinations of nozzle, nozzle holder, nozzle retaining nut, and nozzle opening pressure. To facilitate identification of calibrating nozzle and holder assemblies, they shall be designated in code form as given by the following example:

SAE J968-53-117L




FIGURE 1—CALIBRATING NOZZLE AND HOLDER ASSEMBLY WITH SINGLE HOLE ORIFICE PLATE




FIGURE 2—CALIBRATING NOZZLE AND HOLDER ASSEMBLY WITH DELAY PINTLE TYPE NOZZLE

Dimensions in millimetres




FIGURE 3—HOLDER BODY





FIGURE 4—SPRINGS



Characteristic	Value
Filter clearance (radial)	0,02 mm to 0,033 mm
Filter clearance area	7,3 mm ² min.
Flow area for three flutes (see figure a)	7,5 mm ² min.
Internal volume	1 450 mm ³ ± 40 mm ³
Filter flow at 0,3 MPa (3 bar) pressure ¹⁾	4 750 cm ³ /min to 6 500 cm ³ /min
Minimum flow of assembled holder body with inlet stud and edge filter at 0,3 MPa (3 bar) pressure ¹⁾	2 000 cm ³ /min
1) These tests shall be made using calibration fluid as specified in ISO 4113 at 40 °C ± 1 °C and the tolerance of the supply pressure shall be ± 0,03 MPa (0,3 bar).	

FIGURE 5—CHARACTERISTIC DIMENSIONS AND VALUES OF INLET STUD WITH EDGE FILTER





FIGURE 6—INLET STUD FLOW MEASURING SYSTEM



Orifice plate number		.4	.5	.6	.7	.8
Orifice diameter, mm		0.4	0.5	0.6	0.7	0.8
Flow cm ³ /min	min.	964	1 528	2 190	3 024	3 948
	max.	1 014	1 606	2 302	3 180	4 150

FIGURE 8—SINGE HOLE ORIFICE PLATE

Dimensions in millimetres




FIGURE 9—DISTANCE SLEEVE

SAENORM.COM : Click to view the full PDF of j968_1_201509




FIGURE 10—RETAINING NUTS (CAPNUTS) FOR CALIBRATING NOZZLE AND HOLDER ASSEMBLY
WITH SINGLE HOLE ORIFICE PLATE